

ITEM 5-7, 60, 62, 63


SPECIFICATIONS	
DESCRIPTION:	N.S.F. APPROVED WALK-IN COOLER AND FREEZER COMBO FOAMED-IN PLACE U.L. LISTED, CLASS 1 URETHANE FOAM INSULATION WITH A FLAME SPREAD RATING LESS THAN 25 AND SMOKE DENSITY LESS THAN 450 WHEN TESTING IN ACCORDANCE TO A.S.T.M.-E84 (UL 723)
INSULATION:	WALL, FLOOR AND CEILING PANELS: 4" THICK FOAM PRE-FAB. N.S.F. COVERED FLOOR WITH INTERIOR RAMP INTERIOR / EXTERIOR-26 ga STUCCO EMBOSSED GALVALUM FLOOR FINISH-.10 SMOOTH ALUMINUM
FLOOR:	
FINISH:	
DOOR(S):	(1) 34" x 78" FLUSH IN-FITTING COOLER DOOR (1) 34" x 75" FLUSH IN-FITTING FREEZER DOOR WITH HEATER CABLE ON FOUR SIDE OF OPENING AND THRESHOLD EACH WALK-IN DOOR(S) TO BE EQUIPPED WITH: (2) KASON RIVERSABLE CAM-RISE HINGES MODEL # 1256 (2) KASON SPRING ASSISTED KIT MODEL # 1255 (1) KASON CYLINDER LOCKING HANDLE MODEL # 1229C (1) KASON HYDRAULIC DOOR CLOSER MODEL # 1094
ACCESSORIES:	(2) KASON VAPOR PROOF LIGHT FIXTURE-BASE SURFACE MOUNTED ON INTERIOR TOP PORTION OF DOOR SECTION (PRE-WIRED, GLOBE, CFL Bulbs SHIPPED LOOSE) (2) KASON VAPOR PROOF LIGHT FIXTURE-TO BE SURFACE MOUNTED AND INSTALLED AT JOB SITE ON CEILING PANELS (BASE, GLOBE CFL Bulbs SHIPPED LOOSE) (2) Single Pole Toggle SWITCH AND RED NEON PILOT LIGHT-FLUSH MOUNTED ON EXTERIOR LEG PORTION OF DOOR SECTION AT 45" ABOVE FINISHED FLOOR (PRE-WIRED) (2) 2" dia. DIAL THERMOMETER- FLUSH MOUNTED ON EXTERIOR LEG PORTION OF DOOR SECTION AT 63" ABOVE FINISHED FLOOR. (1) KASON MODEL #1830 PRESSURE RELIEF VENT-FLUSH MOUNTED ON TOP PORTION OF FREEZER DOOR SECTION
ADDITIONAL ACCESSORIES:	1. WALL CLOSURES ON EXPOSED AREAS (SHIPPED LOOSE) 2. COVE BASE ON EXTERIOR (SHIPPED LOOSE)
REFRIGERATION:	(1) 2 HP Low Temp Hermetic Unit 208-230v/60Hz/1φ -3φ (1) EVAPORATOR COIL 230v/60Hz/1φ (-10°F) Hold Temp (1) 1 HP Med Temp Hermetic Unit 208-230v/60Hz/1φ -3φ (1) EVAPORATOR COIL 115v/60Hz/1φ (35°F)
COOLER:	
GENERAL NOTES:	1. CEILING PANEL CAPPED AT FACTORY 2. ALL ELECTRICAL AND PLUMBING WORK BY OTHERS 3. ALL TILE ALLOWED FOR FINISHED FLOOR LINE. 4. ALL DIMENSIONS SUBJECT TO CHANGE UPON FIELD MEASUREMENTS
Alco	
<p><b>PROPRIETARY INFORMATION</b></p> <p>THIS DRAWING IS THE PROPERTY OF KOOL STAR PRODUCTS. IT CONTAINS PROPRIETARY INFORMATION AND IS DISCLOSED IN CONNECTION WITH THE UNDERSTANDING THAT IT WILL NOT BE REPRODUCED OR COPIED DIRECTLY OR INDIRECTLY, AND IS NOT TO BE USED IN WHOLE OR IN PART TO ASSIST IN MAKING OR TO FURNISH ANY INFORMATION FOR THE MAKING OF DRAWINGS OR PRINTS OF APPARATUS EMBODYING FEATURES, DATA OR INFORMATION DERIVED IN ANY MANNER FROM THIS DRAWING WITHOUT THE EXPRESS WRITTEN CONSENT OF KOOL STAR PRODUCTS.</p> <p>NOTE: THESE MATERIALS ARE ALSO PROTECTED UNDER COPYRIGHT LAW AND TREATIES.</p> <p>NOTE FOR CUSTOMER: THIS DRAWING CAN NOT BE CONSIDERED APPROVED UNTIL THE FOLLOWING ITEMS ARE CLARIFIED AND INITIALED.</p> <p>1. VERIFY BUILDING WALL LOCATIONS FOR WALL &amp; CEILING CLOSURES 2. DOOR IS NOT DESIGNED TO ALLOW FOR TILE ON FINISHED FLOOR LINE. 3. VERIFY ELECTRICAL PHASE ON REFRIGERATION UNIT</p> <p><b>DRAWING FOR APPROVAL</b></p> <p>APPROVED BY: _____ DATE: _____</p> <p>NOTE: APPROVAL OF THIS DRAWING ALSO CONSTITUTES ACCEPTANCE OF KOOL STAR'S TERMS AND CONDITIONS AS OUTLINED IN QUOTATION.</p>	

**Kool Star**  
2720 S. Wilmington Ave., Suite 500 • Long Beach, California 90803  
Tel: (310) 562-2007 • Fax: (310) 513-5158

**Wichita Restaurant Supply**  
Assisted Living  
Lake Highlands, TX

DATE: 3/6/10  
REVISED: \_\_\_\_\_  
REVISED: \_\_\_\_\_

SCALE: 1/2" = 1'-0"  
SHEET: 1002-276



**REFRIGERATION:**  
FREEZER:  
2 HP LOW TEMP. HERMETIC UNIT  
UNIT: (1) MHLZ0091 (208-230V/60Hz/1φ -3φ)  
COIL: (1) E1LZ0090 (230V/60Hz/1φ) (-10° F) Holding Temp.  
COOLER:  
1 HP MED. TEMP HERMETIC UNIT  
UNIT: (1) MHHZ0111 (208-230V/60Hz/1φ -3φ)  
COIL: E1HZ0090 (115V/60Hz/1φ) (35°F)

VERIFY PHASE ON UNITS 1φ OR 3φ  
CIRCLE ONE

OUTDOOR PRE-ASSEMBLED REMOTE SYSTEM W/EC MOTORS (CEC COMPLIANT)

